

3 m (10 ft) VGA to HDMI Adapter - USB-Powered - 1080p

Product ID: VGA2HDMM3M



This 3 m (10ft.) VGA to HDMI adapter cable lets you connect the VGA output on your Desktop or Laptop directly to an HDMI input on a monitor, TV, or projector without any additional cords.

High Definition Video

The active VGA to HDMI converter adapts your VGA video output to accommodate the increasing number of displays and projectors that only support HDMI.

Not all VGA converters are created equal. This VGA to HDMI converter cable ensures you're harnessing the highest video quality from your VGA output, with support for resolutions up to 1920x1080 (1080p).

Hassle-Free Setup

For hassle-free setup the VGA (male) to HDMI (male) video cable, allows for plug-and-play installation. Plus, with a built-in USB power cable the device is powered using the USB port on your computer. The VGA to HDMI adapter will work with any computer operating system but when working with a Windows® PC the adapter also supports native USB audio. This functionality allows you to output both sound & video over HDMI.

The Choice of IT Pros Since 1985

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The VGA2HDMM2M is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect a legacy VGA-equipped device to a newer HDMI display
- Connect your VGA-equipped computer to an HDMI home theatre system
- Share video content from your VGA-equipped computer on an HDMI television or projector

Features

- Supports video resolutions up to 1920x1080
- Plug-and-play installation
- USB powered
- USB Audio

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Audio	Yes
	AV Input	VGA
	AV Output	HDMI
	Chipset ID	Micro Silicon - MS9282
Performance	Audio Specifications	HDMI - 7.1 Channel Audio
	Supported Resolutions	HDMI: 1920x1080 (1080p) / 60Hz Additional resolutions and refresh rates may be supported
	Video Revision	HDMI 1.4
	Wide Screen Supported	Yes
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male Input 1 - VGA (15 pin, High Density D-Sub) Male Input
	Connector B	1 - HDMI (19 pin) Male Output
Power	Power Source	USB-Powered
Environmental	Humidity	5%-90% RH
	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-10°C to 55°C (14°F to 131°F)
Physical Characteristics	Color	Black
	Material	Plastic
	Product Height	16.000
	Product Length	115.7 in [294 cm]
	Product Width	40.000
	Weight of Product	178.000
Packaging Information	Package Height	0.010
	Package Length	220.000
	Package Width	200.000
	Shipping (Package) Weight	188.000
What's in the Box	Included in Package	1 - VGA to HDMI Cable

Product appearance and specifications are subject to change without notice.