

HDMI Over Fiber Extender - YUV4:4:4 - 4K 60Hz

Product ID: ST121HD20FXA



This HDMI over Fiber Extender kit lets you transmit your HDMI® audio video signal up to 3300 feet (1000 m) over single-mode fiber, or up to 1000 feet (300 m) over multimode fiber. This converter kit includes both the transmitter and receiver for a complete end-to-end solution.

Astonishing 4K Picture Quality

This HDMI optical extender supports resolutions up to 4K 60Hz (3840 x 2160), providing four times the picture quality of high-definition (1080p). The UHD HDMI Extender supports HDMI 2.0 capabilities, offering 4:4:4 chroma subsampling. This ensures a crystal-clear picture quality and breathtaking color reproduction that is ideal for delivering video content from sources such as Apple TV 4K, Fire TV Stick 4K, or nVidia Shield TV.

Long-Distance Transmission

The Long Range HDMI Extender allows you to extend an HDMI signal up to 3300 feet (1000 m) over single-mode fiber and 1000 feet (300 m) over multimode fiber. Not only is this an incredibly long range solution that can extend an HDMI signal across or between buildings, but because fiber optics transmit data using light rather than copper, it will not cause or be affected by electromagnetic Interference (EMI).

The Choice of IT Pros Since 1985

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

ST121HD20FXA is backed by 2-year StarTech.com warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Features

- Delivers astonishing picture quality with UHD 4K 60Hz up to 3300 feet (1000 m) over single-mode fiber or up to 1000 feet (300 m) over multimode fiber
- No software or drivers required
- Dolby® Atmos, TrueHD, DTS-HD Master Audio, 7.1 channel
- Lifelike colors with HDR and 4:4:4 chroma subsampling support
- Ensured compatibility with HDCP 2.2 devices and displays

Hardware	Warranty	2 Years
	Audio	Yes
	Cabling	Fiber Optic
	Daisy-Chain	No
	Ports	1
	Rack-Mountable	Optional
Performance	Audio Specifications	Supports Dolby® TrueHD, DTS-HD MA, Atmos
	IR Interface	Bi-directional 38Khz / ±10° / 5M
	Max Distance	1 km (0.6 mi)
	Maximum Cable Length	3.3 ft [1 m]
	Maximum Data Transfer Rate	18 Gbps
	Maximum Digital Resolutions	4096 x 2160 (4K) @ 60 Hz
	Supported Resolutions	Single Mode 1000 Meters at 4096 x 2160 60Hz
		Multimode 300 Meters at 4096 x 2160 60Hz
Connector(s)	Wide Screen Supported	Yes
	Local Unit Connectors	1 - HDMI (19 pin) Female
		1 - Fiber Optic LC Simplex Female
		1 - IrDA (Infrared, SIR/FIR) Female
	Remote Unit Connectors	1 - HDMI (19 pin) Female
		1 - Fiber Optic LC Simplex Female
1 - IrDA (Infrared, SIR/FIR) Female		
Power	Center Tip Polarity	Positive
	Input Voltage	100 - 240 AC
	Output Current	1A
	Output Voltage	5V DC
	Plug Type	M
	Power Consumption (In Watts)	3
	Power Source	2 AC Adapters Included
Environmental	Humidity	0-80%
	Operating Temperature	0°C to 40°C (32°F to 104°F)

	Storage Temperature	-10°C to 60°C (14°F to 140°F)
Physical Characteristics	Color	Black
	Material	Steel
	Product Height	18.000
	Product Length	6.3 in [16.1 cm]
	Product Width	68.000
	Weight of Product	282.000
Packaging Information	Package Height	57.000
	Package Length	185.000
	Package Width	250.000
	Shipping (Package) Weight	1012.000
What's in the Box	Included in Package	<ul style="list-style-type: none"> 1 - Local HDMI® Extender Unit 1 - Remote HDMI® Receiver Unit 2 - IR Receiver 2 - IR Blaster 2 - Mounting Brackets 1 - 7ft. [2.1m] Fiber Optic Patch Cable 2 - Foot Pad Set 2 - Universal Power Adapter NA / UK / EU / AU 1 - User Manual

Product appearance and specifications are subject to change without notice.