

**Keyword:**  
**XOL – Extended Operating Life**

**Model:** **SL-889**

**Performance Data** **Size 1/10D**  
 (Typical values for batteries stored at 25°C for one year)


System	Li/SOCl <sub>2</sub>
Nominal voltage	3.6 V
Nominal capacity	1 Ah
Nominal current	0.5 mA
Max. continuous discharge current	10 mA
Max. pulse current capability	20 mA
Anode surface area	7.5 cm <sup>2</sup>
Lithium content	0.3 g
Weight	16 g
Volume	5 cm <sup>3</sup>
Temperature range	-55...+85 °C

**WARNING:**  
 Fire, explosion, and severe burn hazard. Do not recharge, disassemble, heat above 100 °C, incinerate, or expose contents to water.


UL recognition under file MH 12827

See also our website under Products/Safety


**Typical Discharge Curves at +25°C**




**SL-889**



**Available Capacity**



**Operating Voltage**



**Available Terminations**

SL-889 Pins

**Catalogue No.**

11 1 18894 00

Any values given here are for information purposes only. They also depend on actual conditions of use and are not warranties of future performance. Subject to change.