




Data sheet | Item number: 762-4103

Touch Panel 600; 17.8 cm (7.0"); 800 x 480 pixels; 2 x USB, 2 x ETHERNET;
Web Panel



www.wago.com/762-4103



Item description

PIO1 hardware configuration

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



- 2 x ETHERNET port for connecting to field devices and the engineering tool
- 2 x USB port for optional connection of a USB stick, mouse or keyboard

Data

Technical Data

Display diagonal	17,8 cm (7 Inches)
Display	Resistive touchscreen
Display colors	16 million colors
Graphics resolution	(800 x 480) px
Visualization	Webserver
ETHERNET protocols	DHCP DNS FTP FTPS HTTP HTTPS SSH
Communication	Web browser (HTML5)
Operating system	Real-time Linux (with RT-Preempt patch)
Processor	ARM [®] Cortex™ A9
Main memory (RAM)	2,048 MB
Internal memory (flash)	4096 MB
Memory card type	microSD (max. 2 GB); microSDHC (max. 32 GB)
Indicators	five LEDs
Controls	Resistive touch panel, two capacitive keys, proximity sensor
Supply voltage	SELV DC 24 V (18 ... 31,2 V); with reverse voltage protection

Connection data

Connection technology: communication/fieldbus	Web browser: 2 x RJ-45; 2 x USB 2.0 host (type A)
---	---

Geometrical Data

Width	213 mm / 8.386 inch
Height	167 mm / 6.575 inch
Depth	58 mm / 2.283 inch
Panel cutout (W x H)	(198 x 152) mm

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

Mechanical data

Weight	982 g
--------	-------

Environmental Requirements


Surrounding air temperature (operation)	0 ... 55 °C
Surrounding air temperature (storage)	-20 ... 80 °C
Protection type	IP65
Note on protection type	IP65 (front side); IP20 (rear side), per EN 60529
Relative humidity (without condensation)	90 %
Mounting type	Clamping elements (included) or VESA mount (4 x M4x8)

Commercial data


Packaging type	BOX
Country of origin	DE
GTIN	4055143839389
Customs tariff number	8471410000

Approvals / Certificates

Country specific Approvals

Logo	Approval	Additional Approval Text	Certificate name
	KC National Radio Research Agency	Article 58-2, Clause 3	MSIP- REM-W43- WBP762

Ship Approvals

Logo	Approval	Additional Approval Text	Certificate name
	DNV GL Det Norske Veritas, Germanischer Lloyd	-	TAA00001FS

UL-Approvals

Logo	Approval	Additional Approval Text	Certificate name
------	----------	--------------------------	------------------

Subject to changes. Please also observe the further product documentation!



UL
Underwriters Laboratories Inc. (ORDINARY
LOCATIONS)

UL 61010-2-201

E175199

Counterpart

Compatible products

assembling



Item no.: 762-9001
e!DISPLAY7300T ; Clamping elements (4 pieces)

www.wago.com/762-9001

Downloads Documentation

Manual

WAGO Touch Panel 600 Standard Line	1.2.0 Apr 7, 2020	pdf 2.9 MB	Download
---------------------------------------	----------------------	---------------	----------

Bid Text

762-4103 docx - Datei	Dec 21, 2018	docx 21.4 kB	Download
--------------------------	--------------	-----------------	----------

System Description

Touch Panel 600, system description		pdf 727.2 kB	Download
-------------------------------------	--	-----------------	----------

Runtime Software

Firmware

Firmware: 762-4103 Touch Panel 600; 17.8 cm (7.0"); 800 x 480 pixels; 2 x USB, 2 x ETHERNET; Web Panel	15 Dec 9, 2019	zip 150.6 MB	Download
--	-------------------	-----------------	----------

Handling Instructions

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

Data sheet | Item number: 762-4103

www.wago.com/762-4103



Product family

Standard Line

[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.