


## PHYSICAL DIMENSIONS



Cap: G13

## PRODUCT FEATURES

- Fluorescent Lamp with 26 mm diameter.
- Available light colours: *Cool Daylight* (765), *Cool White* (640)

## Technical Data

Frequency	(Hz)	:	50 Hz-Operation
Lamp wattage	(W)	:	15
Nominal current (CCG-operation) uncompensated	(A)	:	0,31
Lamp arc voltage UL after switch-on ( $\pm 10\%$ )	(V)	:	55

## Life Time\*

Average life time (50% failure rate)	(h)	:	13000 (CCG)
Economical life time (80% lum. flux from initial 100h value)	(h)	:	5000 (CCG)

## PHOTOMETRICAL DATA

Labelling in brand OSRAM	Rated luminous flux** (lm)	Colour rendering index (R <sub>a</sub> )	Colour temperature (K)
L 15W/765	740	70...79	6500
L 15W/640	850	60...69	4000

\*\* at 50 Hz operation and aged 100h; 25°C ambient temperature

**Note:** \*Measurement in accordance with EN 60081, annex C.  
 The lamps meet EN 60081 and EN 61195 requirements.  
 Starter and ballasts have to meet EN 60155 and EN 60921 requirements.

