

Sabre™ WTW, WTB Power System

7.5mm Pitch



- 2 - 6 circuits wire to wire or wire to board
- Board locks for 0.062" thick PCBs
- Patented new TPA (Terminal Position Assurance) on mated terminals
- Virtually eliminates terminal backout
- Anti-tangle positive latches
- Polarised Housing
- Terminals fully isolated in housings
- For 14 - 18 AWG wire

Voltage	100V mated, 600V unmated	Temperature range	-40°C to 130°C
Current rating	18A	Housing	Nylon UL94V-0
Dielectric voltage	6000V	Contacts	Brass, Plating
Insulation resistance	1000Mohm		

Mftrs. List No.	Description	Order Code
43178-2002	female terminal - insulation diameter 3.3mm	101-2197
43375-0001	female terminal - insulation diameter 3.3mm	973-4090
43375-1001	female terminal - insulation diameter 4.57mm	973-4104
43680-2002	2 way plug	329-2939
43680-2004	4 way plug	329-2952
44441-2002	2 way receptacle	329-2988
44441-2003	3 way receptacle	329-2990
44441-2004	4 way receptacle	329-3002
44441-2005	5 way receptacle	329-3014
44441-2006	6 way receptacle	329-3026
43160-3102	2 way header SMC r/a with board lock	329-3038
43160-3103	3 way header SMC r/a with board lock	329-3040
43160-3104	4 way header SMC r/a with board lock	329-3051
43160-3106	6 way header SMC r/a with board lock	329-3075
43160-2102	2 way header SMC vertical with board lock	973-4112
43160-2103	4 way header SMC vertical with board lock	101-2199
43160-2104	4 way header SMC vertical with board lock	973-4120
43160-2105	6 way header SMC vertical with board lock	101-2200
43160-2106	female crimp hand tool 2.36-3.56mm dia	101-2201
638117200	female crimp hand tool 2.36-3.56mm dia	142-2487
63813-0500	female extraction tool	329-3166
63813-0800	male extraction tool	329-3180

Order Multiple 2	No of Ways	Mftrs. List No.	Order Code	Price Each
Plug				
	2	43680-2002	329-2939 ●	
	4	43680-2004	329-2952 ●	
Receptacle				
	2	44441-2002	329-2988 ●	
	3	44441-2003	329-2990 ●	
	4	44441-2004	329-3002 ●	
	5	44441-2005	329-3014 ●	
	6	44441-2006	329-3026 ●	
R/angled Hdr				
	2	43160-3102	329-3038 ●	
	3	43160-3103	329-3040 ●	
	4	43160-3104	329-3051 ●	
	6	43160-3106	329-3075 ●	
Vertical Hdr				
	2	43160-2102	973-4112 ●	
	3	43160-2103	101-2199 ●	
	4	43160-2104	973-4120 ●	
	5	43160-2105	101-2200 ●	
	6	43160-2106	101-2201 ●	
Terminals				
Order Multiple = 20				
Female 3.3mm		43178-2002	101-2197 ●	
Female 3.3mm		43375-0001	973-4090 ●	
Female 4.57mm		43375-1001	973-4104 ●	

209523

Mftrs. List No.	Description	Order Code	Price Each
638117200	Female crimp hand tool 2.36-3.56mm ins dia	142-2487	
63811-7300	3.05-4.57mm ins dia	145-3583	
63813-0500	Insertion tool	329-3166	
63813-0800	Extraction tool	329-3180	