

## Coaxial Cable Connector 11\_UHF-0-7-17/033\_-

### Description

Straight cable plug

Interface standards  
IEC 60169-12



### Technical Data

#### Electrical Data

Impedance other  $\Omega$   
Interface frequency max. 0.2 GHz

#### Mechanical Data

Centre contact crimped  
Outer contact crimped  
Weight 0.0238 kg

#### Environmental Data

Operating temperature -55 °C to 165 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PSU (Polysulfone)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing DOU-00181576  
Catalogue drawing DCA-00045040  
Assembly instruction DOC-0000201061

### Ordering Information

Single package 11\_UHF-0-7-17/033\_-E

### Additional Information

Suitable cables RG\_213\_/U, GX\_07272, G\_07262, G\_07272, RADOX\_RF\_213