

Coaxial Cable Connector 11_716-50-9-9/033_-

Description

Straight cable plug

QUICK-FIT connector
 For outdoor applications
 Water protection according to IP 68



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	7.5 GHz	
Frequency range	DC to 2.5 GHz	2.5 to 3 GHz
Return loss	≥ 30 dB	≥ 27 dB
Intermodulation	≤ Static -155 dBc (2 x 43 dBm carrier)	

Mechanical Data

Centre contact	plugged
Outer contact	clamped
Weight	0.1264 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	NR (Natural Rubber)	

Related Documents

Outline drawing	DOU-00006217
Catalogue drawing	DOU-00006219
Assembly instruction	DOC-0000179418

Ordering Information

Single package	11_716-50-9-9/033_-E
----------------	----------------------

Additional Information

Suitable cables	SUCOFEED_1/2_HF, SUCOFEED_1/2_HF_FR, SUCOFEED_1/2_HF_FR_UL, Heliax FSJ4-50B, NK Cables RFF 1/2-50, Cellflex SCF12-50, FlexLine 1/2 S
Interface standards	IEC 61169-4_CECC 22190_DIN 47223_VG 95250