



32" HD LED Digital TV

- 32" HD Ready widescreen LED TV
- Built-in Freeview T2 HD and Digital Freeview Channels
- HDMI input for your external devices and consoles
- Can be wall mounted (100mm x 100mm)

	EAN	5060062269819
Specifications	Model No.	C3220DVB
	Chipset	MSD3663
	Sales Market	England
	VESA Size	100 x 100
	Wall Mount Screws	M5 x 8
	Speaker Output	2 x 8W
	Actual Size of Display (Diagonal)	31.5"

Display	Display Type	LED
	Resolution	1366 x 768 (16:9)
	Brightness (nit)	200
	Contrast	3000:1
	Display Colours	16.7M
	Refresh Rate	60Hz
	Viewing Angle H/V	178/178
	Reponse Time	8.5ms

Accessories	Remote	1
	Battery	AAA x 2
	User manual	English

Terminals		
HDMI Input		2
RCA Component + AUDIO Input		1
RCA Composite + AUDIO Input		1
12-PIN VGA + AUDIO Input		1
RF Input		1
Optical Digital AUDIO Input		1
Coaxial Digital AUDIO Input		0
Analog AUDIO Output		0
3.5mm Headphone Output		1

Features		
DVD		No
DVB-S		Without
DVB-S2		Without
DVB-T+C		With
DVB-T2+C		With
CI		With
3D Digital Comb Filter + 3D Noise Reduction		Yes
Automatic Volume Control		Yes
Sleep Timer		Yes
NO Signal Shut Down		Yes
Adjustable Bass & Treble Controls		Yes
Adjustable Balance Control		Yes
Picture Modes		Standard/Dynamic/Soft/User
Preset Sound Modes		Standard/Music/Movie/User
OSD Menu Language		English/French/Spanish/Italy/Germany/Portugal
Aspect Ratio Modes		Wide/Zoom/Cinema/Normal
PVR Function		Recording standby, time-shift EPG recording reservation

Power		
Power Supply		AC120-230,50-60Hz
Power Consumption		75W
Standby Consumption		<0.5W

Dimension		
Unit Dimensions w Stand		730.26 x 468.88 x 195.29
Unit Dimensions w/o Stand		730.26 x 430.76 x 94
Carton Box Dimensions		