
Product Datasheet 12V MR16 Dichroic Halogen Lamps



Type	Beam Angle (degrees)	Voltage (V)	Wattage (W)	Cover Colour	Colour Rating	Life (Hours)
GU5.3/GX5.3	12	12	20	Clear	2800k	2,000
GU5.3/GX5.3	24	12	20	Clear	2800k	2,000
GU5.3/GX5.3	36	12	20	Clear	2800k	2,000
GU5.3/GX5.3	12	12	35	Clear	2900k	2,000
GU5.3/GX5.3	24	12	35	Clear	2900k	2,000
GU5.3/GX5.3	36	12	35	Clear	2900k	2,000
GU5.3/GX5.3	13	12	50	Clear	3000k	2,000
GU5.3/GX5.3	24	12	50	Clear	3000k	2,000
GU5.3/GX5.3	38	12	50	Clear	3000k	2,000

Available as in a variety of power and beam angle variants with ex-stock availability for:

Code	Description
MR16H20W12	MR16 Low Voltage Halogen Lamp 20W 12 Degrees
MR16H20W24	MR16 Low Voltage Halogen Lamp 20W 24 Degrees
MR16H20W36	MR16 Low Voltage Halogen Lamp 20W 36 Degrees
MR16H35W12	MR16 Low Voltage Halogen Lamp 35W 12 Degrees
MR16H35W24	MR16 Low Voltage Halogen Lamp 35W 24 Degrees
MR16H35W36	MR16 Low Voltage Halogen Lamp 35W 36 Degrees
MR16H50W13	MR16 Low Voltage Halogen Lamp 50W 13 Degrees
MR16H50W24	MR16 Low Voltage Halogen Lamp 50W 24 Degrees
MR16H50W38	MR16 Low Voltage Halogen Lamp 50W 38 Degrees

Features

- Lamp life up to 2,000 hours – Clear Cover
- Aluminium coated reflector
- Manufactured under ISO9000
- CE Approved and RoHS Compliant