








## NiCd (nickel cadmium) battery packs

	Battery pack voltage V	Capacity of battery pack Ah	Order no.
<b>NiCd (nickel cadmium) battery packs, series 1</b>			
	4,8	1,2	6.31101
	7,2	1,4	6.30069
	9,6	1,4	6.30070
	9,6	1,7	6.30072
	12	1,7	6.30073
	12	2	6.31723
<b>NiCd (nickel cadmium) battery packs, series 2</b>			
	9,6	1,7	6.30065
	12	2	6.31724
	14,4	1,7	6.30067
	14,4	2	6.31725
<b>NiCd (nickel cadmium) battery packs, series 3</b>			
	9,6	1,4	6.31746
	9,6	2	6.31728
	12	1,25	6.31737
	12	1,4	6.31747
	12	2	6.31729
	12	2,4	6.31748
	15,6	1,25	6.31738
	15,6	2,4	6.31749
	18	1,25	6.31739
	18	2,4	6.31740
<b>NiCd battery packs "AIR COOLED"</b>			
	9,6	1,4	6.25470
	9,6	2	6.25471
	12	1,4	6.25473
	12	2	6.25474
	14,4	1,4	6.25475
	14,4	2	6.25476
	18	1,4	6.25477
	18	2	6.25478

## NiMH (nickel-metal hydride) battery packs


	Battery pack voltage V	Capacity of battery pack Ah	Order no.
<b>NiMH battery packs, series 1</b>			
	9,6	3	6.31775
	12	3	6.31776
	15,6	3	6.31777
<b>NiMH battery packs "AIR COOLED"</b>			
	12	3	6.25479
	14,4	3	6.25480
	18	3	6.25481

## Li-Ion battery packs "AIR COOLED"


	Battery pack voltage V	Capacity of battery pack Ah	Order no.
	12 <sup>1)</sup>	2,2	6.25486
	14,4 <sup>2)</sup>	2,2	6.25482
	18 <sup>3)</sup>	2,2	6.25484

1) at maximum voltage, nominal voltage 10,8 Volts  
 2) at nominal voltage, maximum voltage 16 Volts  
 3) at nominal voltage, maximum voltage 20 Volts

## NiCd battery pack for Bh EA 14 S- R+L

	Battery pack voltage V	Capacity of battery pack Ah	Order no.
	14,4	4	6.31727

## Adapter for old Metabo chargers

	Order no.
 For using old battery packs (from 1981 on) in the new "AIR COOLED" chargers, as well as for using "AIR COOLED" batteries in old chargers	6.27075

## Carry case

	Order no.
	6.25440
<b>Carry case BS/BSP/SBP</b> for BSP 12 Plus, BSP 15,6 Plus and chargers AC 30, C 45 for SBP 12 Plus and chargers AC 30, C 45	

	6.25441
<b>Carry case SBT/BSP/SBP</b> for BSP 12 Plus, BSP 15,6 Plus, BSP 18 Plus and chargers ACS 15, AC 30, ICS 10, C 45 for SBP 12 Plus, SBP 18 Plus and chargers ACS 15, AC 30, ICS 10, C 45	

	6.24634
<b>Metabox II for cordless tools</b> for BS 9.6 , BST 9.6 , BS 9.6 Impuls, BST 9.6 Impuls, BS 12 Impuls, BST 12 Plus, BS 15.6 Plus, BST 15.6 Plus, BS 18 Plus, SB 12 Plus, SB 15.6 Plus for BST range 9.6-18 V, BS range 9.6-18V, SBT 9.6-18 V and chargers C 45, ACS 15 Not suitable for BSZ range! Dimensions: 395 x 295 x 157,5 mm	

HAMMERS  
 IMPACT DRILLS  
 DRILLS  
 CORDLESS DEVICES  
 SCREW-DRIVERS  
 ANGLE GRINDERS  
 SANDING MACHINES  
 ROUTERS AND PLANERS  
 SAWS  
 SPECIAL MACHINES  
 HEDGE TRIMMERS  
 METABOXES