



light source

work equipment
connected load
Power consumption
colour temperature
color rendering index (CRI)
System of protection
class of protection
technology
operation
luminaire body
lamp cover
tubular sections
balance of articulation joints
weight (net)
mains lead

Fastening

lens; dimensions
lens material
lens; diopters
add-on lens; dimensions
special features

LED
Energy efficiency category A/A+/A++
electronic transformer
100/120/220-240 V; 50/60 Hz
approx. 12 W
neutral white, approx. 3800 K
>= 95
IP20
I
multi-stage switchable
switch
plastic, black
screen, milky
steel tube, painted, black
spring
approx. 4.4 kg
approx. 3.0 m; mains plug
CEE 7/II
screw-down flange, table clamp (accessory), wall bracket (accessory)
175 x 105 mm
glass
3
not available
ESD version



CEE 7/II

illuminance

Comment: I
distance: 15 cm

Em: 3015 lx
Emax: 4266 lx
Emin: 1434 lx

