



Fiberglass Handle Bolt Cutter, 24-1/2-Inch



All-purpose, center-cut jaws for soft, medium, and hard metals. The orange fiberglass handles have heavy vinyl grips with flat grips ends for 90-degree cuts.

Specifications

Soft & Medium Cutting Max Capacity:	7/16" (11.1 mm)	Hard Material Cutting Max Capacity:	5/16" (0.8 cm)
Handle Material:	Fiberglass	Handle Color:	Orange
Replacement Blade:	63924	Overall Length:	24.5" (62.2 cm)
Weight:	6.1 lb (2.8 kg)		