



Steel-Handle Bolt Cutter, 42-Inch



All-purpose, center-cut jaws for soft, medium, and hard metals. Forged, alloy tool steel jaws are precision ground for sure, efficient cutting and long life. The red steel handles have heavy vinyl grips with flat grips ends for 90-degree cuts.

Specifications

Soft & Medium Cutting Max Capacity:	1 1/16" (17.5 mm)	Hard Material Cutting Max Capacity:	1/2" (1.3 cm)
Handle Material:	Steel	Handle Color:	Red
Replacement Blade:	63842	Overall Length:	42" (106.7 cm)
Weight:	19.2 lb (8.7 kg)		