

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201088305](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), WSOR Cable, 22 AWG, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
 Series [120108](#)
 Connector End A Micro-Change (M12)
 Connector End B Micro-Change (M12)
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (M12)
 Protocol EtherNet
 Type Double Ended
 UPC 889056150507

Physical

Cable Diameter 6.80mm
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Green
 Coupling Style Threaded
 Gender Male-Male
 Keyway D-coded
 LED Indicator No
 Material - Cable Jacket TPU
 Material - Connector Body TPU
 Material - Coupling Nut Brass
 Material - Plating Mating Gold
 Net Weight 184.219/g
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -20°C to +60°C
 Wire Size AWG 22
 Wire/Cable Type Shielded TPU

Electrical


Current - Maximum per Contact 1.5A
 Voltage - Maximum 30V

Material Info

Engineering Number E11A06012M020

Reference - Drawing Numbers

Sales Drawing SD-120108-072-001



EU ELV

Not Reviewed

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

Search Parts in this Series

[120108 Series](#)