

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300370011](#)
Status: **Active**
Overview: DeviceNet Solutions
Description: DeviceNet Micro-Change (M12), Top Mount, 8 Port, 5 Pole, with Micro-Change Connector on 2.0m Cable

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Passive Distribution Boxes
 Series [130037](#)
 IP Rating IP67
 Overview [DeviceNet Solutions](#)
 Product Name DeviceNet, Micro-Change (M12)
 UPC 78678840557

Physical

Bus I/O Micro-Change (M12)
 Cable Connector Orientation Straight
 Cable Length 2.0m
 Home Run Cable Length 2.0m
 Home Run Connector Micro-Change (M12) - 5 pole
 Home Run Interface Cable - Side Entry
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Housing PBT
 Material - Metal Copper
 Material - Plating Mating Gold
 Orientation Top Mount
 Poles 5
 Poles (wired) 5
 Ports 8
 Temperature Range - Operating -20°C to +90°C
 Wiring Configuration Single I/O per Port

Electrical


Current - Maximum per Contact 4.0A per port
 Functional Wiring Parallel
 Voltage - Maximum 10-30V DC

Material Info

Engineering Number DND8500-02

Reference - Drawing Numbers

Sales Drawing SD-130037-006



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per
 -ED/01/2018 (15
 January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130037](#) Series