

**MNX PCM 95/75 T**



Sample photo

**Order symbol:** PCM 95/75 T  
**Product nbr:** 6016932  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074054807  
**EI. number:**  
 Finland: 3421398  
 Electric No. 8212027598  
 Denmark:  
 Electric No. Sweden: 2535401

Including: Base with metric knock-outs and PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	100	100	75	MIN 8	DIN-15 Mounting rail
inch:	3.9	3.9	3.0	B-3	DIN-35 Mounting rail
				FP 22046	Wall fastening lug (4 pcs)

Materials:		Rating:
<b>Material:</b>	Polycarbonate	Ingress Protection (EN 60529): IP66/IP67
<b>Base colour:</b>	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
<b>Cover screws material:</b>	Polyamide	Electrical insulation: Totally insulated
<b>Cover colour:</b>	Smoked grey	Halogen free (DIN/VDE 0472, Part 815): 1
<b>Cover screws colour:</b>	Black	UV resistance: UL 508
<b>Gasket material:</b>	Polyurethane	Flammability Rating: UL 746C 5"
		Glow Wire Test (IEC 695-2-1) °C: 960
		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:		Certificates:
<b>Temperature °C (short term):</b>	-40 ... 120 °C	SGS Fimko
<b>Temperature °C (continuous):</b>	-40 ... 80 °C	
<b>Temperature °F (short term):</b>	-40 ... 250 °F	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F	

Accessories:	
MIV 95	Mounting plate (Galvanized steel)

