

## PAR CAN WITH RGBWA COB LED 5-IN-1 - 50W

### PARLED50-COB

PAR can fitted with a high power 5-in-1 COB LED that produces ultra bright beams in red, blue, green, white and amber and a mix of these.

- 9x DMX channels
- Stand-alone, master-slave, DMX & remote controlled operation
- Variable electronic strobe
- Electronic dimmer with linear curve
- LCD display
- Wide projection angle of 60°
- Remote control

**EAN CODE** **5420047134585**  
**16-2030**

### SPECIFICATIONS TECHNIQUES

Power supply	220-240Vac 50/60Hz
Consumption	70W
Light source	1 RGBWA COB LED 5-in-1 of 50W
Projection angle	60°
Weight	1kg
Dimensions	190 x 190 x 150mm



### LOGISTICS VALUES

Height	15 cm
Width	19 cm
Depth	19 cm
Net weight	900 kg
Packaging height	15 cm
Packaging width	20.5 cm
Packaging depth	20.5 cm
Packaging volume	0.006 m <sup>3</sup>
Packaging gross weight	1000 kg
Master carton height	32 cm
Master carton width	43 cm
Master carton depth	43 cm
Master carton net weight	8 kg
Master carton gross weight	12 kg
Qty per packaging	1
Qty per master carton	8
EAN14 code	54200471345858
Customs code	94054091

