

4-IN-1 RGBW LED PAR CAN WITH SMD LED STROBE

PAR-MINI-STR

Small DMX controlled PAR can fitted with a high power SMD LED strobe.

- 8x DMX channels
- PAR can fitted with 3 x 4W RGBW 4-in-1 LEDs
- LED strobe featuring 18x 0.5W SMD LED
- Auto, DMX, sound or remote controlled
- RGB Color mix (>16.7 million colors)
- Linear dimmer 0-100%

EAN CODE **5420047134448**
16-2010

SPECIFICATIONS TECHNIQUES

Power supply	100-240Vac 50/60Hz
Consumption	15W
PAR	3x 4W 4-in-1 RGBW LED
Strobe	18x 0.5W white SMD 5730LED
Beam angle	25°
Dimensions	12.5 x 12.5 x 12.5cm
Weight	600g



LOGISTICS VALUES

Height	12 cm
Width	12.5 cm
Depth	12 cm
Volume	1E-06 m ³
Net weight	0.5 kg
Packaging height	12.5 cm
Packaging width	13 cm
Packaging depth	12.5 cm
Packaging volume	0.002 m ³
Packaging gross weight	0.6 kg
Master carton height	27.5 cm
m carton largeur	66 cm
m carton profondeur	40 cm
m carton volume	0.0726 m ³
m carton poids net	19 kg
m carton poids brut	19 kg
Palette hauteur	1 cm
Palette largeur	0.8 cm
Palette profondeur	1.2 cm
Qty per packaging	1
Qty per shipping box	30
nb uvc par palette	270
nb couches parpalette	3
nb cartons par couche	3
EAN14 code	54200471344486
Customs code	94054091

