



BT3660 with nuisance call blocking and answer machine

Block nuisance calls

Nuisance Call blocking features

Avoid nuisance and unwanted calls with our new BT3660. Block up to 50 specific numbers or use the dedicated Do Not Disturb key to silence your calls.

Easy set up and great sound quality

Get the most out of your phone straight away with our easy to use menu and great sound.

Main features

- Block up to 50 numbers
- Excellent sound quality
- Easy set up
- Handsfree speaker
- Long range reception, up to 300m outdoors, 50m indoors
- 10 hours of talking OR 100 hours standby time
- See and hear if you have a second call waiting
- Easy to read screen shows when you have messages
- Dedicated Do Not Disturb button
- Save up to 50 contacts
- Redial any of the last 10 calls you made
- Record up to 12 minutes of messages
- 1.6 inch blue backlit screen



Specification

GAP compatible	Yes	Hands free	Yes	Text message memory	No
Max. number of handsets	4	Headset socket	No	Call waiting indicator	Yes
Max. number of bases	1	Auto answer	Yes	PBX access code	No
Bluetooth registered handsets	N/A	Find key on base	Yes	Repeater 240compatible	No
Conference call	Yes	Secrecy /Mute	Yes	Wall Mount	No
Call transfer	Yes	Handset naming	Yes	Talk time	10 hours
Internal calls	Yes	Keypad lock	No	Standby	100 hours
Music on hold	No	Power on/off	Yes	Battery type	NiMH
Indoor range ¹ (Metres)	50	Inductive coupler	No	Battery size	AAA
Outdoor range ¹ (Metres)	300	Earpiece volume control	Yes	Battery capacity	300
Display type	Mono	Hands free volume control	Yes	Base PSU item code	094906
Display-number of lines ²	1	Call timer	Yes	Charger PSU item code	094906
Backlit	Yes	Clock	Yes	SIM card	No
Contrast control	No	Alarm	Yes	Caller groups	No
Wallpapers	No	Calendar	No	Quick dial memories	2
Screen saver	No	Appointments	No	Handset settings PIN protected	Yes
Handset polyphonic ringtones	No	Illuminated keypad	N/A	Base settings Pin protected	Yes
Handset standard ringtones	5	Keypad confirmation tone	Yes	Low battery indicator	Yes
Handset ringer on/off	Yes	Associated ring tone	Yes	Low battery alert	Yes
Handset ringer volume control	Yes	Base ringtones	5	Out of range indicator	Yes
Visual ring indicator	Yes	Base ringer on/off	Yes	Out of range alert	Yes
Answer Machine					
Recording time (mins)	Up to 12	Answer delay	Yes	Call screening	Yes
Playback	Handset & base	Time saver	Yes	Memo	Yes
Outgoing messages	2	Remote access	Yes	Timed TAM	No
Recordable outgoing messages	Yes	Message advice	Indicator		
Do Not Disturb					
DND Button	Yes				

1 In ideal conditions

2 Including icons and soft keys as appropriate

3 You must subscribe to a Caller Display service from your network provider for nuisance calls blocking, text messaging and visual voicemail features. Charges may apply.

Technical support

Available from the BT Helpdesk on 0800 145 6789 or via the email link on the product page at www.bt.com/producthelp

Offices worldwide

The services described in this publication are subject to availability and may be modified from time to time. Services and equipment are provided subject to British Telecommunications plc's respective standard conditions of contract. Nothing in this publication forms any part of any contract.

© British Telecommunications plc 2018
Registered office: 81 Newgate Street, London EC1A 7AJ. Registered in England No: 1800000.
Template 2.0

Draft 1 / March 2018

Supplier data

	Dimensions H x W x D	Weight Empty / Complete	Manufactured in China Status – In Development	
Product			Item code	CSS codes
Base	4.3 x 10.9 x 14.3 cm	121.4 g	Single: 093665	TBC
Handset	14.9 x 5.1 x 2.5 cm	90.4 g	Twin: 093666	TBC
Charger	4.0 x 8.5 x 11.0 cm	57.4 g	Trio: 093667	TBC
Gift box			Barcodes	Over pack barcodes
Single	14.6 x 20.0 x 7.0 cm	63.00 / 409.40 g	5016351619865	05016351826034
Twin	14.6 x 19.0 x 11.0 cm	76.20 / 667.00 g	5016351619872	05016351826041
Trio	14.6 x 20.8 x 12.2 cm	90.80 / 932.60 g	5016351619889	05016351826058
Over pack			Gift boxes per over pack	Pallet Ti's x Hi's
Single	21.6 x 37.4 x 32.4 cm	337.0 / 4431.00 g	10	9 x 4
Twin	20.6 x 46.2 x 32.4 cm	374.8 / 5710.80 g	8	7 x 4
Trio	18.1 x 37.4 x 17.9 cm	362.2 / 5957.80 g	6	15 x 5

