



Portable Radio Frequency Receiver

RF-RX1

Our lightweight Portable Radio Frequency Receiver provides high-quality sound sent from our range of transmitters and transceivers. It has a transmission range of up to 300 metres in open air, and there is no limit to the number of receivers which can be used per group. The unit uses a micro-USB power supply for fast and simple charging in a variety of situations.

Physical Data

Dimensions	Height – 85mm (3.34") Width – 50mm (1.96") Depth – 15mm (0.59")
Weight	64g (0.14lbs)
Finish	Grey

Technical Data

Power Supply	Lithium-Ion rechargeable battery 3.7V / 1100mAh (inbuilt)
Battery Life	Approx. 10 hours
Transmission Frequency	2.4GHz (ISM band)
Modulation	FSK, with hopping
Transmission Range	300m in open air / 100m in buildings
Channels	40 simultaneous groups
Frequency Response	50Hz – 7kHz
Transmission Power	10mW
Sensitivity	-95dBm
Data Rate	2Mbps
Connectors	2 x 3.5mm 4 contact-socket
	Micro-USB charge port

Applications

Ideal for situations where listeners require clear sound, tour guidance or interpretation:

- Museums
- Historical Sites
- Meeting Rooms
- Conferences
- Places of Worship

Components

- Portable Radio Frequency Receiver
- Earphones
- Belt Clip
- USB Charger Cable
- Lanyard

Accessories

- 2 Bay Charging Station [RF-RX-CS2]
- 20 Bay Charger Case [RF-DC20]
- Inductive Neck Loop [IR-NL1]
- Headphones [IR-HP1]
- Underchin Headphones [IR-HP2]

Talk to us now:
+44 (0) 1732 223900 (UK & ROW)
+1 616 392 3400 (US & Canada)
www.contacta.co.uk

