

DYMO®



LabelManager™ 280

CREATE LABELS FAST WITH SMART KEYS

Customize labels using the PC or MAC® connectivity to import your own fonts and graphics


Features

- Large LCD display
- Computer-style keyboard
- One-touch Smart Keys for fast formatting
- Long lasting rechargeable battery pack
- 20+ ways to format text
- 200+ symbols and clip-art images
- Print up to 1/2 in (12 mm) wide labels
- For even more features, download DYMO® Connect for Desktop Software



Single Unit Includes:

- LabelManager 280
- Rechargeable Lithium-Ion Battery
- D1 Starter Label Cassette, 12mm x 3m Black on White
- USB Cable
- Charging Adapter
- Quick Start Guide
- 2 + 1 - Year Limited Warranty*



Kit Includes:

- LabelManager 280 + Softcase Bag
- Rechargeable Lithium-Ion Battery
- 2x D1 Label Cassette, 9mm x 7m Black on Clear | 12mm x 7m Black on White
- USB Cable
- Charging Adapter
- Quick Start Guide
- 2 + 1 - Year Limited Warranty*



Quick Specs

| | |
|-----------------------------|--|
| Unit Dimensions (H x W x L) | 107.5 x 206 x 46.5 mm |
| Weight (excluding battery) | 810 g |
| Mac®/PC Compatible | Yes via DYMO® Connect for Desktop Software |
| Accepts Label Sizes | 6mm, 9mm and 12mm |
| Tape Platform | D1, Durables |
| Resolution | 180 dpi |
| Printing System | Thermal Transfer |
| Print Speed | 15 mm/sec |
| Barcodes | Yes via DYMO® Connect for Desktop Software |
| Cutter Type | Manual |
| Batteries | Rechargeable |
| AC Adapter | Yes (included) |
| Networking | No |
| Country of Origin | China |


| Item Number | Description | | Length (cm) | Width (cm) | Height (cm) | QTY | EAN | Customer Price |
|-----------------------------------|-----------------------------|------|-------------|------------|-------------|-----|---------------|----------------|
| S0968920 | LabelManager 280 QWERTY | Unit | 8.9 | 19.0 | 24.0 | 1 | 3501170968925 | |
| S2091152 | LabelManager 280 QWERTY KIT | Unit | 20.5 | 10.2 | 5.7 | 1 | 3026980911522 | |
| Accessories (www.dymo.com) | | | | | | | | |
| S0895900 | Charging Adapter | Unit | 9.0 | 4.8 | 8.2 | 1 | - | |

* +1 year if registered on the Dymo website

D1 Standard Polyester Labels

For hundreds of tasks around the office or home office, such as filing, storage and asset tracking.
Temperature rating: -18°C to 90°C

| D1 STANDARD LABELS (3 m) | 6 mm | 9 mm | 12 mm |
|------------------------------|----------|----------|----------|
| ABC | - | - | 2084349 |
| ABC | - | - | 2084401 |
| D1 STANDARD LABELS (7 m) | 6 mm | 9 mm | 12 mm |
| ABC | S0720780 | S0720680 | S0720530 |
| ABC | S0720770 | S0720670 | S0720500 |
| ABC | S0720790 | S0720730 | S0720580 |
| ABC | - | S0720710 | S0720560 |
| ABC | - | S0720740 | S0720590 |
| ABC | - | S0720720 | S0720570 |
| ABC | - | - | S0720610 |
| ABC | - | S0720690 | S0720540 |
| ABC | - | - | S0720510 |
| ABC | - | - | S0720600 |
| ABC | - | S0720700 | S0720550 |
| ABC | - | - | S0720520 |
| D1 STANDARD MULTIPACKS (7 m) | 6 mm | 9 mm | 12 mm |
| ABC | - | 2093096 | 2093097 |



D1 Durable Vinyl Labels

Industrial strength adhesive helps to ensure labels stay stuck to a variety of surfaces.
Temperature rating: -40°C to 80°C

| D1 DURABLE LABELS (3 m) | 12 mm |
|---------------------------|---------|
| ABC | 1978366 |
| ABC | 1978365 |
| ABC | 1978367 |
| D1 DURABLE LABELS (5.5 m) | 12 mm |
| ABC | 1978364 |



D1 Permanent Polyester Labels

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins and more.
Temperature rating: -40°C to 150°C*

| D1 PERMANENT POLYESTER (5.5 m) | 12 mm |
|--------------------------------|----------|
| ABC | S0718060 |

*depends on surface



D1 Flexible Nylon Labels

Specifically designed for curved surfaces and wire and cable marking.
Temperature rating: -40°C to 60°C

| D1 FLEXIBLE NYLON (3.5 m) | 12 mm |
|---------------------------|----------|
| ABC | S0718040 |



The DYMO® high quality labels are made in Belgium