

DYMO®

LabelManager™ PnP



PLUG AND PLAY LABEL MAKER

Customize labels with your own fonts and graphics using built-in, ready-to-use software. Simply plug the device into a PC or MAC® to get started.


Features

- Customize labels using fonts and graphics from your computer
- Built-in, ready-to-use DYMO® software with PC and MAC® connectivity
- USB chargeable battery
- Print up to 1/2 in (12 mm) wide labels
- For even more features, download DYMO Connect



Single Unit Includes:

- LabelManager PnP
- Rechargeable Lithium-Ion Battery
- D1 Starter Label Cassette, 12mm x 3m Black on White
- USB Cable
- Quick Start Guide
- 2 + 1 - Limited Warranty*



Quick Specs

Unit Dimensions (H x W x L)	52.6 x 135.7 x 141 mm
Weight (excluding battery)	275 g
Mac®/PC Compatible	Yes via DYMO Connect
Accepts Label Sizes	6mm, 9mm and 12mm
Tape Platform	D1, Durables
Resolution	180 dpi
Printing System	Thermal Transfer
Print Speed	12 mm/sec
Barcodes	Yes
Cutter Type	Manual
Batteries	Rechargeable
Adapter	No, charges via USB cable (included)
Networking	No
Country of Origin	China


Item Number	Description		Length (cm)	Width (cm)	Height (cm)	QTY	EAN	Customer Price
S0915390	LabelManager PnP	Unit	8.0	17.3	22.2		3501170915394	

* +1 year if registered on the Dymo website

D1 Standard Polyester Labels

For hundreds of tasks around the office or home office, such as filing, storage and asset tracking.
Temperature rating: -18°C to 90°C

D1 STANDARD LABELS (3 m)	6 mm	9 mm	12 mm
ABC	-	-	2084349
ABC	-	-	2084401
D1 STANDARD LABELS (7 m)	6 mm	9 mm	12 mm
ABC	S0720780	S0720680	S0720530
ABC	S0720770	S0720670	S0720500
ABC	S0720790	S0720730	S0720580
ABC	-	S0720710	S0720560
ABC	-	S0720740	S0720590
ABC	-	S0720720	S0720570
ABC	-	-	S0720610
ABC	-	S0720690	S0720540
ABC	-	-	S0720510
ABC	-	-	S0720600
ABC	-	S0720700	S0720550
ABC	-	-	S0720520
D1 STANDARD MULTIPACKS (7 m)	6 mm	9 mm	12 mm
ABC	-	2093096	2093097



D1 Durable Vinyl Labels

Industrial strength adhesive helps to ensure labels stay stuck to a variety of surfaces.
Temperature rating: -40°C to 80°C

D1 DURABLE LABELS (3 m)	12 mm
ABC	S1978366
ABC	1978365
ABC	1978367
D1 DURABLE LABELS (5.5 m)	12 mm
ABC	1978364



D1 Permanent Polyester Labels

Professional, polished finish ideal for panels, blocks, faceplates, shelves, bins and more.
Temperature rating: -40°C to 150°C*

D1 PERMANENT POLYESTER (5.5 m)	12 mm
ABC	S0718060

*depends on surface



D1 Flexible Nylon Labels

Specifically designed for curved surfaces and wire and cable marking.
Temperature rating: -40°C to 60°C

D1 FLEXIBLE NYLON (3.5 m)	12 mm
ABC	S0718040



The DYMO high quality labels are made in Belgium