

**ModuPlug
HDC MRJ45 A MI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

| | |
|------------|---|
| Type | HDC MRJ45 A MI |
| Order No. | 2592220000 |
| Version | Module, Plug insert, RJ45 tool-free, TIA-568A |
| GTIN (EAN) | 4050118602333 |
| Qty. | 1 pc(s). |

Data sheet

ModuPlug HDC MRJ45 A MI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 0.21 g

Temperatures

Limit temperature -40 °C ... 70 °C

Environmental Product Compliance

REACH SVHC Potassium perfluorobutane sulfonate 29420-49-3

General data

| | | | |
|------------------------------|---|--------------------------------------|--------------------|
| Insulating material | PC glass-fibre reinforced (UL-listed and railway-certified) | Insulation strength | 10 ¹² Ω |
| Material | Polycarbonate, glass fibre reinforced | Number of poles | 8 |
| Plugging cycles | 750 (RJ45) | Pollution severity | 3 |
| Rated current (DIN EN 61984) | 1 A | Rated impulse voltage (DIN EN 61984) | 0.8 kV |
| Rated voltage (DIN EN 61984) | 50 V | Required plug-in slots | 1 |
| Series | ModuPlug | Surge voltage category | III |
| Type | Pin | UL 94 flammability rating | V-0 |

Classifications

| | | | |
|-------------|-------------|------------|-------------|
| ETIM 6.0 | EC002312 | ETIM 7.0 | EC002312 |
| eClass 9.0 | 27-44-02-92 | eClass 9.1 | 27-44-02-18 |
| eClass 10.0 | 27-44-02-92 | | |

Downloads

Engineering Data [STEP](#)

Data sheet

**ModuPlug
HDC MRJ45 A MI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

