




FGxx, FGxxK, LFGxx, EFxx, LFKx



METAL FAN GUARDS, IP20



FG25



FGxxx

Finger Guards for standardized Fan sizes 25x25mm up to 172x150mm. Material: steel wire chromium plated.


Art. No.	Type	Fan Size [mm]	D [mm]	Nbr. of Rings	Height [mm]	Packing [PCs]
912510000	FG25 Fan Guard	25x25	1x28.2	2	5	100
913010000	FG30 Fan Guard	30x30	4x24	2	5	100
914010000	FG40 Fan Guard	40x40	4x32	2	5	100
915010000	FG50 Fan Guard	50x50	4x42	3	5	100
915010001	FG50-40 Fan Guard	50x50	4x40	3	5	100
916010000	FG60 Fan Guard	60x60	4x50	4	5	100
918010000	FG80 Fan Guard	80x80	4x71.5	5	5	100
919210000	FG92 Fan Guard	92x92	4x82.5	6	5	100
911210000	FG120 Fan Guard	120x120	4x105	8	5.7	100
915110000	FG150 Fan Guard	172x150	1x162	9/10	6.5	100
917210000	FG172 Fan Guard	D172	1x162	10	6.5	100

LFKxx



POWER LEADS FOR AC-FANS

Purpose of product: Quick connection or disconnection of fans with standard terminal male plugs. 2.8x0.3mm, colour black, length 960 mm, straight head (other types on request). UL E207628.




Art. No.	Type	for AC-Fans with standard terminals	Length [mm]	Colour	Packing [PCs]
911032000	Fan Power Lead	LFK1vz	910	black	50

DUST- AND EMC FILTERS, THREE-PART IP30, EMC-SCREENS

The plastic filter of the LFG series offers an IP30 level of protection, according to publication IEC592. Its components are the fan guard, the clip-on lid and the filter blanket. By replacing the plastic frame with an EMC-frame (silver), a cost effective dust+EMC-filter develops.

When the filter blanket is saturated with dust, it can be vacuum cleaned or washed with water and detergent and used again. We recommend regular cleanups, depending on the dust contamination in the environment to avoid a decrease in performance.

Filter blanket, plastic fan guard and EMC fan guard are offered separately also. Plastic material: (ABC/PC) according to UL 94V-0.



Art. No.	Type	for Fan Size [mm]	Dimension WxH [mm]	Packing [PCs]
924020045	LFG40-45 Dust Filter three-part	40x40mm, IP30	46.4x6.5	100
926020045	LFG60-45 Dust Filter three-part	60x60mm, IP30	64x12.2	100
928020045	LFG80-45 Dust Filter three-part	80x80mm, IP30	86x12.2	100
929220045	LFG92-45 Dust Filter three-part	92x92mm, IP30	97x12.2	100
921220045	LFG120-45 Dust Filter three-part	120x120mm, IP30	126x13	100
914020000	FG40K Plastic Fan Guard	40x40mm, IP20	42.3x3.3	100
916020000	FG60K Plastic Fan Guard	60x60mm, IP20	60x6.0	100
918020000	FG80K Plastic Fan Guard	80x80mm, IP20	81x5.5	100
919220000	FG92K Plastic Fan Guard	92x92mm, IP20	92x5.5	100
911220000	FG120K Plastic Fan Guard	120x120mm, IP20	121x6.5	100
916030000	EMVG60 EMC Fan Guard	60x60mm, IP30	60x6.0	100
918030000	EMVG80 EMC Fan Guard	80x80mm, IP30	81x5.5	100
919230000	EMVG92 EMC Fan Guard	92x92mm, IP30	92x5.5	100
911230000	EMVG120 EMC Fan Guard	120x120mm, IP30	121x6.5	100
924020045	EF40 Filter Blanket	40x40mm, IP30	-	100
926020145	EF60 Filter Blanket	60x60mm, IP30	-	100
928020145	EF80 Filter Blanket	80x80mm, IP30	-	100
929220145	EF92 Filter Blanket	92x92mm, IP30	-	100
921220145	EF120 Filter Blanket	120x120mm, IP30	-	100
936010400	FM60 EMC Screen	60x60mm, IP40	60x4.0	100
938010400	FM80 EMC Screen	80x80mm, IP40	84x3.5	100
939210400	FM92 EMC Screen	92x92mm, IP40	92x4.0	100
931210400	FM120 EMC Screen	120x120mm, IP40	119x3.5	100
931510400	FM150 EMC Screen	D150mm, IP40	182/162x4.2	50