

General ordering data

Qty	500
Order No.	0354361187
Short text for material	DEK 5 FWZ L1-PE
EAN	4008190047054

Markings

Qty	500
-----	-----

Markers

Printed characters	Mixed characters
Printing method	MC Laser
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Pin can be written (STI)	No
Speed marking laser	No
Silicone	no
Pitch	5,00 mm
Can be written with plotter	No
Orientation of printing	horizontal
Can be written with dot-matrix printer	*UNDEFINED TEXT*
Material colour according to resistance code	9
Colour	white
Material	Polyamide
Colour of printing	black
Type of printing	Standard
PrintJet	No
Can be labelled with thermal transfer printers	No
Can be written with laser printer	No
Length	5 mm
Halogens	no
Function	Connector marker
Cadmium	no
Width	5 mm
UL 94 flammability rating	V2

Classifications

ETIM 2.0	EC000761
ETIM 3.0	EC000761
eClass 4.1	24-19-02-19
eClass 5.0	27-14-11-37
eClass 5.1	27-14-11-37

Related products

Order No.	Short text for material
0133161114	DEK 5 FW U1-PE1
0133161123	DEK 5 FW U10-PE1

0133161115	DEK 5 FW U2-PE2
0133161116	DEK 5 FW U3-PE3
0133161117	DEK 5 FW U4-PE4
0133161118	DEK 5 FW U5-PE5
0133161119	DEK 5 FW U6-PE6
0133161120	DEK 5 FW U7-PE7
0133161121	DEK 5 FW U8-PE8
0133161122	DEK 5 FW U9-PE9
0133261150	DEK 5 FW X1-Z1
0133261159	DEK 5 FW X10-Z10
0133261151	DEK 5 FW X2-Z2
0133261152	DEK 5 FW X3-Z3
0133261153	DEK 5 FW X4-Z4
0133261154	DEK 5 FW X5-Z5
0133261155	DEK 5 FW X6-Z6
0133261156	DEK 5 FW X7-Z7
0133261157	DEK 5 FW X8-Z8
0133261158	DEK 5 FW X9-Z9
0354361203	DEK 5 FWZ L1-EIK
0558360000	DEK 5 FWZ U,V,W,N,PE
2123690000	DEK 5 FWZ WS 1-8,+,-,
0576261198	DEK 5 GW +
0576261199	DEK 5 GW -
0576291741	DEK 5 GW BL/SW -
0576261202	DEK 5 GW ERDE
0576261203	DEK 5 GW ERDE I.KR.
0522361075	DEK 5 GW L1
0522361076	DEK 5 GW L2
0522361077	DEK 5 GW L3
0537261235	DEK 5 GW MP
0537261187	DEK 5 GW PE
0537261188	DEK 5 GW PEN
0576291737	DEK 5 GW RT/SW +
0576261215	DEK 5 GW W-STROM