

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2157101123](#)  
**Status:** **Active**  
**Overview:** [Off-the-Shelf Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead Clik-Mate Male-to-Clik-Mate Male, Tin (Sn) Plated, 225.00mm Length, 24 AWG, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                        |                                                 |
|------------------------|-------------------------------------------------|
| Product Family         | Cable Assemblies                                |
| Series                 | <a href="#">215710</a>                          |
| Application            | Signal, Wire-to-Board                           |
| Assembly Configuration | Pre-crimped Lead Only                           |
| Connector to Connector | CLIK-Mate-to-CLIK-Mate                          |
| Overview               | <a href="#">Off-the-Shelf Pre-Crimped Leads</a> |
| Product Name           | CLIK-Mate                                       |
| UPC                    | 193264604982                                    |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 225.00mm             |
| Circuits (Loaded)              | 1                    |
| Color - Resin                  | Black                |
| Gender                         | Male-Male            |
| Material - Metal               | Copper Alloy         |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Net Weight                     | 0.797/g              |
| Packaging Type                 | Bag                  |
| Plating min - Mating           | 0.406µm              |
| Plating min - Termination      | 0.406µm              |
| Single Ended                   | No                   |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 0.78-1.28mm          |
| Wire Size AWG                  | 24                   |
| Wire/Cable Type                | UL 10002             |

**Electrical**

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 2.0A             |
| Voltage - Maximum             | 100V AC (RMS)/DC |

**Material Info**

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 2157101121-000 |
|---------------|----------------|



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ECHA\_01\_2020 (16  
January 2020

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[215710 Series](#)

**Use With**

[CLIK-Mate Housing 502578](#) , [503149](#)