



L1325/Ni FLEXIBLE TERMINAL BLOCK

- Heavy duty flexible terminal block
- 12 way

CURRENT RATING:	43A (temperature rise <20° C above ambient)
TEMPERATURE RANGE:	-55° C to +70° C (ambient)
VOLTAGE PROOF:	4 KV rms
INSULATION RESISTANCE:	≥1000 megohms
CREEPAGE DISTANCE	
BETWEEN TERMINALS:	10.7mm
TERMINALS TO CHASSIS:	6.3mm
HUMIDITY:	Class H6 (DEF-5011)
WIRE SIZE (MAXIMUM):	7/1.35mm
WEIGHT (AVERAGE):	158g
APPROVALS	DEF-5011

ORDERING REFERENCE: L1325/Ni



BLP reserve the right to change without prior notice the information contained within this leaflet

BLP Components Ltd., Exning Road, Newmarket, Suffolk, CB8 0AX, England
Tel: +44 (0)1638 665161 Fax: +44 (0)1638 660718 email: sales@blpcomp.com <http://www.blpcomp.com>