







PA27 wp

**Pillar Terminal Block
with Wire Protector
(12 poles)**



TECHNICAL DATA

	IEC Standards	American Standards	
Ratings	450V - 24A	300V - 15A	
Wire size	2.5 sqmm	18 ÷ 14AWG	
Working Temperature	- 5 ÷ 125°C (short time 155°C)	23 ÷ 221°F	
Plastic Material	Polyamide PA6.6 natural colour, UL94 V2		
Metal Parts	Cage insert made in nickel plated brass; M3 Captive screw made in zinc plated steel; Wire protector made in stainless steel		
Accessories	PA36 - PA37 - PA295 - PA228 - PA52 - PA197		
Approvals	File Nr.	Ratings (sqmm/AWG - V - A - T)	Standard References
	CA02.01048	2.5 sqmm - 450V - 24A - 125°C	EN 60998-1; EN 60998-2-1
	CA02.01048	2.5 sqmm - 450V - 24A - 125°C	EN 60998-1; EN 60998-2-1
	40013746	2.5 sqmm - 450V - 24A - 125°C	DIN EN 60998-1; DIN EN 60998-1/A1; DIN EN 60998-2-1 (VDE 0613)
	E76048 vol. 1 sec. 1	18 ÷ 14 AWG - 300V - 15A - 105°C	UL 1059; CSA C22-2 N.158-1987

PACKAGING

Type	P-N	Pack.	Dim. Pack. (LxHxP)	Weight (Kg)
PA 27 WP/12P	PA27XA1F12P	500	40x20x40	16.5

DIMENSIONAL
DRAWING

