








PA35wp

**Pillar Terminal Block
with Wire Protector
(12 poles)**



TECHNICAL DATA

	IEC Standards	American Standards
Ratings	450V - 17.5A	300V - 6A
Wire size	1.5 sqmm	20 ÷ 18AWG
Working Temperature	-5 ÷ 125°C (short time 155°C)	23 ÷ 221°F
Plastic Material	Polyamide PA6.6 natural colour, UL94 V2, GWT 960°C	
Metal Parts	Cage insert made in nickel plated brass; M3 Captive screw made in zinc plated steel; Wire protector made in stainless steel	
Accessories	PA52	

Approvals	File Nr.	Ratings (sqmm/AWG - V - A - T)	Standard References
	CA02.00597	1.5 sqmm - 450V - 17.5A - 125°C	EN 60998-1; EN 60998-2-1
	CA02.00597	1.5 sqmm - 450V - 17.5A - 125°C	EN 60998-1; EN 60998-2-1
	121212	1.5 sqmm - 450V - 17.5A - 125°C	DIN EN 60998-1; DIN EN 60998-2-1 (VDE 0613)
	E76048 vol. 1 sec. 1	20 ÷ 18 AWG - 300V - 6A - 105°C	UL 1059; CSA C22-2 N.158-1987
	LR 40455	20 ÷ 14 AWG - 300V - 6A	CSA C22-2 N.158-1987; E.C.N 584B

PACKAGING

Type	P-N	Pack.	Dim. Pack. (LxHxP)	Weight (Kg)
PA 35WP/12P	100112	1000	40x20x40	21.0

DIMENSIONAL
DRAWING

