

MEACO UK LIMITED	
DD8L	
Type of dehumidifier	Desiccant compressor-free
Extraction rate	8L/day at all conditions in operating range
Air heater	Delivers air 10-12°C warmer than room temperature when drying
Humidistat	Electronic with intuitive icons & laundry mode
Continuous drainage option	Yes, length of drainage hose included
Child lock	No
Timer	Yes, turns off after 1,2,4 or 8 hours, to save power once clothes are dry
Electronic controls	Yes
Auto restart	Yes
Ioniser	Yes
Filter	Yes , washable
Noise level	39/43/48dB(A)
Power Supply	220V-240V / 50Hz
Power Consumption	30/330/650 Watts
Fan Speeds	3
Operating Temperatures	1°C 40% RH to 37°C
Refrigerant	NONE - No Compressor Desiccant model
Tank	2 Litres
Dimensions (HWD) mm	500 x 351 x 188
Weight	6.4 Kgs