

# INLINE FUSE HOLDER FOR JCASE® STYLE FUSES (Std. & LP)

RoHS



## Specifications

Maximum Voltage Rating:	58V
Maximum Current Rating:	See table below.
Cable Insulation	GXL, 125°C
Operating Temperature Range:	-40°C to +125°C
Max. Fuse Insertion Force:	49N

## Ordering Information

Part Number	Package Size
0FHJxxxxG	250
FHJCxxxxG	250
HLJCxxxxG	250
0FHJxxxxL	50
FHJCxxxxL	50
HLJCxxxxL	50

## Description

This product is an Inline fuse holder for use with either standard or Low Profile JCASE® fuses, 20A - 60A. It offers size and weight savings compared to MAXI® fuseholders, and has an optional protective cover for splash resistance. Standard product will have two 102mm red wire leads. Wire length and insulation color can be customized upon request. Tinned wires also available upon request. All customizations have minimum order requirements. Contact Littelfuse sales representative for details.

There are two available mounting options: One version with mounting brackets, and one without.

## Ratings

Part Number	Description	Cover	Mounting	Wire Size	Fuse Rating
0FHJ1001_	Standard JCASE Holder	None	—	10AWG	40 A max
0FHJ1002_	Standard JCASE Holder	None	—	8AWG	60 A max
0FHJ2001_	Standard JCASE Holder	None	Mounting Bracket	10AWG	40 A max
0FHJ2002_	Standard JCASE Holder	None	Mounting Bracket	8AWG	60 A max
FHJC1001_	Standard JCASE Holder	Yes	—	10AWG	40 A max
FHJC1002_	Standard JCASE Holder	Yes	—	8AWG	60 A max
FHJC2001_	Standard JCASE Holder	Yes	Mounting Bracket	10AWG	40 A max
FHJC2002_	Standard JCASE Holder	Yes	Mounting Bracket	8AWG	60 A max
HLJC1001_	Low Profile JCASE Holder	Yes	—	10AWG	40 A max
HLJC1002_	Low Profile JCASE Holder	Yes	—	8AWG	60 A max
HLJC2001_	Low Profile JCASE Holder	Yes	Mounting Bracket	10AWG	40 A max
HLJC2002_	Low Profile JCASE Holder	Yes	Mounting Bracket	8AWG	60 A max

# INLINE FUSE HOLDER FOR JCASE® STYLE FUSES (Std. & LP)

RoHS

**Dimensions**

Dimensions in mm

"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	INSULATION TYPE
102.0	102.0	9.0	9.0	RED	RED	GXL (STANDARD)

