

# Front plate - ECS-P-122X169-S-UV1-2RJ45 - 1143740

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

ECS family faceplate, ready for integration of two VARIOSUB RJ45 VS-08 connectors, screw locking, rated IP66/67/69 when combined with ECS housing, Color: Black (9005), Width: 163 mm, Height: 30 mm, Depth: 62 mm




## Your advantages

- Effective protection of electronics against thermal and mechanical influences
- Housing design supports the installation of a range of PCB thicknesses for high application diversity
- Optional pressure compensation membrane for fluctuating ambient pressure
- Optional accessories for wall and mast mounting



## Key Commercial Data

Packing unit	1
GTIN	 4 063151 131159
GTIN	4063151131159
Custom tariff number	85389099

## Technical data

### Item properties

Type	ECS-P-122X169-S-UV1-2RJ45
Order No.	1143740
Housing type	outdoor housings
Type	Screw locking
Connection	Prepared for 2x RJ45 socket insert
Impact strength	IK08
Mounting type	Screw locking
Type of locking	screw locking

### Measurements

Width [ w ]	163 mm
Height [ h ]	30 mm

## Front plate - ECS-P-122X169-S-UV1-2RJ45 - 1143740

### Technical data

#### Measurements

Depth [ d ]	62 mm
-------------	-------

#### Material specifications

Flammability rating according to UL 94	V0
Housing material	PC (polycarbonate)

#### PCB data

Number of PCB holders	1
PCB thickness	1.59 mm ... 2.36 mm

#### Packaging information

Pieces per package	5
Denomination packing units	Pcs.

#### Standards and regulations

Flammability rating according to UL 94	V0
--	----


#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Drawings

# Front plate - ECS-P-122X169-S-UV1-2RJ45 - 1143740

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 5.0	EC000058
----------	----------