

EDIFIER®

R1280T

Technology. Style. Utility. You can have it all.

Equipped with dual RCA inputs the Studio 1280T can produce up to 42W RMS of audio output. A 4 inch bass driver and front facing bass reflex port ensures bass notes are robust and rich in sound.

Connect to multiple devices and personalize your listening experience with the bass and treble adjustment dials located on the active speaker. A remote control also controls the volume and mute function.



42
watts
R.M.S
TOTAL POWER OUTPUT



Features

- Active bookshelf speaker system with 42W total power output
- Dual RCA inputs for connectivity to multiple audio sources
- Bass, treble and master volume dials located on the side panel
- Wireless remote control for volume adjustment and mute
- Calibrated, flared front-facing bass reflect port
- 100% MDF wooden enclosures to minimize acoustic resonance
- Universal 100V-240V power supply

Specifications

Power Output	: RMS 21W × 2
Signal to noise ratio	: ≥85dBA
Frequency response	: 75Hz~18KHZ
Input sensitivity	: LPC: 750mV ± 50mV Aux: 550mV ± 50mV
Input type	: RCA - 3.5mm Auxiliary, RCA
Bass driver	: 4", 6Ω, with bass reflection port
Treble driver	: 13mm silk dome tweeter, 4Ω
EAN code	: 6923520265084 (UK)



Disclaimer: All specifications are subject to change without notice

www.edifier.com

A Passion for Sound