

PRODUCT-DETAILS

AMD60344-AN

AMD60344-AN - Universal/LED rotary dimmer - 1M - AN



General Information

| | |
|-----------------------|---|
| Extended Product Type | AMD60344-AN |
| Product ID | 2CLA626030N1801 |
| EAN | 8427238138404 |
| Catalog Description | AMD60344-AN - Universal/LED rotary dimmer - 1M - AN |
| Long Description | <p>Rated voltage: 230 Vac \pm 10%. Frequency: 50 Hz (Nominal power: 250 W/VA) / 60 Hz (Nominal power: 200 W/VA). Power (min./max load): - LEDi: 2 / 100 W/VA (max. 10 lamps). - Dimmable energy saving lamps: 2 / 100 W/VA (max. 10 lamps). - LV LEDi with transformer (only type L or LC): 4 / 100 W/VA (max. 10 lamps). - Incandescent lamps: 10 / 250 W/VA. - Halogen lamps: 10 / 250 W/VA. - LV halogen with transformer (only type L or LC): 10 / 250 W/VA (max. 10 lamps). 2 wire connection. Optional: auxiliary on/off with 2-way switch N2X02. Indicator LED lamp included. Back-up fuse: Electronic. Overload protection: Electronic. Ambient temperature: 0° C to +35° C. Combination with frames AMD5144-XX & 5244-XX</p> |

Ordering

| | |
|-----|---------------|
| EAN | 8427238138404 |
|-----|---------------|

| | |
|------------------------|----------|
| Minimum Order Quantity | 1 piece |
| Customs Tariff Number | 85365080 |

Dimensions

| | |
|----------------------------|---------|
| Product Net Width | 0.076 m |
| Product Net Height | 0.064 m |
| Product Net Depth / Length | 0.076 m |
| Product Net Weight | 0.08 kg |

Container Information

| | |
|--------------------------------|---------------|
| Package Level 1 Units | 1 piece |
| Package Level 1 Width | 0.076 m |
| Package Level 1 Height | 0.064 m |
| Package Level 1 Depth / Length | 0.076 m |
| Package Level 1 Gross Weight | 0.08 kg |
| Package Level 1 EAN | 8427238138404 |

Environmental

| | |
|-------------------------|--|
| Ambient Air Temperature | Operation -5 ... +35 °C Storage -5 ... +50 °C |
|-------------------------|--|

Additional Information

| | |
|---------------------------------|--|
| Actuator Type | Turn button |
| Color | Anthracite |
| Connection Type | Screw |
| Degree of Protection | IP20 |
| Frequency (f) | 50...60 Hz |
| Function | Dimmer, Universal/LED, 2M |
| Load Type | Resistive load |
| Material | Plastic |
| Mounting Type | Flush mounted (plaster) |
| Product Main Type | Millenium |
| Product Name | Universal/LED rotary dimmer - 1M - AN |
| Rated Voltage (U _r) | 230...230 V |
| Replaced Product ID (OLD) | 2CL0DN626038 |
| Surface Finishing | Surface protection: Decor Surface finishing: Matt |

Certificates and Declarations (Document Number)

| | |
|-----------------------------------|-----------------------|
| Data Sheet, Technical Information | 9AKK106930A7740 |
| Declaration of Conformity - CE | No declaration needed |
| Instructions and Manuals | 2CLX226039N1001 |

Classifications

| | |
|---------------|--|
| ETIM 5 | EC000025 - Dimmer |
| ETIM 6 | EC000025 - Dimmer |
| ETIM 7 | EC000025 - Dimmer |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |

Categories

Low Voltage Products and Systems → Switch Assortments → Flush Mounted Range BS - Niessen → Design Millenium → Flush Mounted Inserts with Cover Plate → Dimmers

Low Voltage Products and Systems → Switch Assortments → Light / LoadControl → Electronic Rotary / Push Button Dimmer (all Loads incl. LED, DALI) → Push Button Dimmer - Flush Mounted → Dimmers

