

PRODUCT-DETAILS

LB6

LB6 Soldering Socket



General Information

Extended Product Type	LB6
Product ID	GJL1201902R0001
EAN	4013614051074
Catalog Description	LB6 Soldering Socket
Long Description	LB6 Soldering Receptacle 5-pole

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85366990

Popular Downloads

Data Sheet, Technical Information	1SBC100173C0201
Dimension Diagram	GJL1200421

Dimensions

Product Net Width	47.5 mm
Product Net Height	44 mm
Product Net Depth / Length	40 mm

Product Net Weight	0.02 kg
--------------------	---------

Technical

Rated Operational Current AC-3 (I _e)	(500 V) 55 °C 8 A (690 V) 55 °C 3.5 A
Rated Insulation Voltage (U _i)	690 V
Standards	UL 60947-1 UL 60947-4-1
Conventional Free-air Thermal Current (I _{th})	Auxiliary Circuit 10 A Main Circuit 10 A
Product Name	Soldering Socket
Suitable For	B6-F BC6-F B6S-F B7-F BC7-F K6-F KC6-F
Suitable for Product Class	Mini Contactors

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 300 V AC Auxiliary Circuit 300 V AC
Ampere Rating UL/CSA	Main Circuit 8 A Auxiliary Circuit 8 A

Environmental

Ambient Air Temperature	Operation -25 ... +50 °C Storage -25 ... +55 °C Storage -40 ... +80 °C
-------------------------	--

Certificates and Declarations (Document Number)

ABS Certificate	NoCerNee
BV Certificate	NoCerNee
cULus Certificate	1SAA938003-1701
Declaration of Conformity - CE	1SAA938004--4402
DNV Certificate	NoCerNee
GL Certificate	NoCerNee
LR Certificate	NoCerNee
RINA Certificate	NoCerNee
RMRS Certificate	NoCerNee
UL Certificate	1SAA938000-1604

Container Information

Package Level 1 Width	115 mm
Package Level 1 Depth / Length	280 mm
Package Level 1 Height	54 mm
Package Level 1 Gross Weight	0.27 kg
Package Level 1 EAN	4013614412387

