

Non-Reversible OMEGALABEL™ Temperature Labels



- ✓ Adhesive Backs for Easy Mounting for Temperatures Above -40°C/°F
- ✓ Indicator Turns Black When Exposed


TL-8 and TL-10 Range Series

Specifications

Accuracy: Up to 99°C (210°F) is ±1°C (1.8°F);
 From 100°C (212°F) to 154°C (309°F) is ±1.5°C (2.7°F);
 From 160°C (320°F) to 280°C (536°F) is ±1% and ±1°C (1.8°F)



Confirm correct shipping of critical products.




TL-8 SERIES,
 8-Temperature Range Labels
 46 x 18 mm (1.8 x 0.7")

| Model No. | Temperature Range | | | | | | | | | |
|-------------|-------------------|-----|-----|-----|-----|-----|-----|-----|-----|--|
| TL-8-105(*) | °F | 105 | 110 | 115 | 120 | 130 | 140 | 150 | 160 | |
| | °C | 40 | 43 | 46 | 49 | 54 | 60 | 66 | 71 | |
| TL-8-170(*) | °F | 170 | 180 | 190 | 200 | 210 | 220 | 230 | 240 | |
| | °C | 77 | 82 | 88 | 93 | 99 | 104 | 110 | 116 | |
| TL-8-250(*) | °F | 250 | 260 | 270 | 280 | 290 | 300 | 310 | 320 | |
| | °C | 121 | 127 | 132 | 138 | 143 | 149 | 154 | 160 | |
| TL-8-330(*) | °F | 330 | 340 | 350 | 360 | 370 | 380 | 390 | 400 | |
| | °C | 166 | 171 | 177 | 182 | 188 | 193 | 199 | 204 | |
| TL-8-410(*) | °F | 410 | 420 | 435 | 450 | 465 | 480 | 490 | 500 | |
| | °C | 210 | 216 | 224 | 232 | 241 | 249 | 254 | 260 | |


TL-8-250 shown actual size.

* Insert "-10" for package of 10 or "-30" for package of 30.
Ordering Example: TL-8-170-30, 8 temperature range labels (170, 180, 190, 200, 210, 220, 230, 240°F), package of 30.



Applications

- General • Aeronautical • Electrical • HVAC
- All applications where size is not a conditioning factor




TL-10-105 shown actual size.

TL-10 SERIES, 10-Temperature Range Labels
 54 x 18 mm (2.1 x 0.7")

| Model No. | Temperature Range | | | | | | | | | | |
|--------------|-------------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| TL-10-105(*) | °F | 105 | 110 | 115 | 120 | 130 | 140 | 150 | 160 | 170 | 180 |
| | °C | 40 | 43 | 46 | 49 | 54 | 60 | 66 | 71 | 77 | 82 |
| TL-10-190(*) | °F | 190 | 200 | 210 | 220 | 230 | 240 | 250 | 260 | 270 | 280 |
| | °C | 88 | 93 | 99 | 104 | 110 | 116 | 121 | 127 | 132 | 138 |
| TL-10-290(*) | °F | 290 | 300 | 310 | 320 | 330 | 340 | 350 | 360 | 370 | 380 |
| | °C | 143 | 149 | 154 | 160 | 166 | 171 | 177 | 182 | 188 | 193 |
| TL-10-390(*) | °F | 390 | 400 | 410 | 420 | 435 | 450 | 465 | 480 | 490 | 500 |
| | °C | 199 | 204 | 210 | 216 | 224 | 232 | 241 | 249 | 254 | 260 |

* Insert "-10" for package of 10 or "-30" for package of 30.
Ordering Example: TL-10-105-30, 10 temperature range labels (105, 110, 115, 120, 130, 140, 150, 160, 170, 180°F), package of 30.

Test PC board components.



Shown smaller than actual size.