

METER COIL RESISTANCE

Ω RANGE	ITEM			
	SD-38	SD-60	SD-80	SD-506
DC 100uA	1500Ω	1500Ω	1500Ω	
DC 1mA	40Ω	40Ω	40Ω	
DC 20mA	40Ω	40Ω		
DC 500mA	40Ω			
DC 1A	6Ω	6Ω	6Ω	
DC 3A	6Ω			
DC 5A	6Ω	6Ω	6Ω	0.01Ω
DC 10A		6Ω	6Ω	0.01Ω
DC 15A		6Ω		0.01Ω
DC 20A				0.01Ω
DC 30A		6Ω	6Ω	
DC 50A		6Ω	6Ω	
DC 12V				1.3KΩ
DC 15V	40Ω	40Ω	40Ω	2.3KΩ
DC 24V				3KΩ
DC 30V	40Ω	40Ω	40Ω	3KΩ
DC 300V		40Ω	40Ω	

**P.S. ** SD-301 : 650Ω±10%, 500uA ±15% (STANDARD) OR
ACCORDING TO YOUR SPECIFICATION.

THREAD SIZE OF SCREWS

	SD-38	SD-60	SD-80
A	3 x 5 , P:0.5	5/32x1/4, 32W	5mm, P: 0.9
B	2.3x12, P:0.4	1/8x1/2, 40W	1/8x1/2, 40W

A : INPUT TERMINALS

B : FOUR LEGS FOR INSTALLATION