



Item Code – US207

KAUDEN™ CAT6A Shielded RJ45 Inline Cord Coupler – High Quality UL Listed



- Fully shielded inline coupler for CAT6A structured wiring systems
- RJ45 - female to female - Pin 1 to Pin1 – For CAT6A Screened Twisted Pair Cable (STP)
- UL Listing assures superior construction and performance compared to non-listed products
- CAT6A specifies performance characteristics for frequencies up to 500MHz
- Small and compact-21x35x16mm, backwards compatible with CAT6 and CAT5E

Enabling the easy joining of two RJ45 terminated cables specified as CAT6A or any lower specification. The UL listing means that extra mechanical and signaling performance is assured due to the superior construction.



Item Code – US207      Data Sheet

**General**

Sale Unit	Single unit. Polybag with barcode
Barcode	5028088011942
Commodity Code	85177000
Dimension Packed	90x80x16mm    Height Width Depth
Dimension loose	21x35x16mm    Height Width Depth
Weight Packed	9 grams
Weight Loose	8 grams

**Outer Carton information for Trade and Bulk buyers**

Carton Quantity	tba
Dimension	9.5x15x26cm
Weight	tba

**Pin out schematic**

RJ45	RJ45
Pin	Pin
1 to	1
2 to	2
3 to	3
4 to	4
5 to	5
6 to	6
7 to	7
8 to	8