



Classic filament LED candles and lusters

Classic LEDLuster D 5-40W P45 E27 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	E27 [E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	5-40W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	94.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	5 W

Lamp Current (Nom)	38 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	5 kWh


Classic filament LED candles and lusters

Product Data

Full product code	871869670992400
Order product name	Classic LEDLuster D 5-40W P45 E27 827 CL
EAN/UPC - Product	8718696709924
Order code	929001332602
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001332602
Net Weight (Piece)	0.014 kg


Dimensional drawing




Candle P45 4.5-40W 470lm 2700K D Clear

Product	D	C
Classic LEDLuster D 5-40W P45 E27 827 CL	45 mm	80 mm


Photometric data



LEDbulb, Bulb A21 14W, 18W 2200-2700K




LEDbulb 40W E27 827 CL P45




LEDbulb 40W E14 827 CL B35

Classic filament LED candles and lusters

Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

