



CorePro LEDcapsule MV

CorePro LEDcapsule ND 1.9-25W G9 827

The LED specialties deliver a high quality light to make themselves to be a true replacement of halogen specialty lamp (such as G9 and R7S). It is particularly suit for task lighting in hotel and restaurants, and ideal for decorative and ambient application. LEDspecialty products deliver huge energy saving and minimize maintenance costs, without any compromise on light quality.

Product data

General Information	
Cap-Base	G9 [G9]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	30000X
Technical Type	1.9-25W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	204 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	107.37 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 Hz
Power (Nom)	1.9 W


Lamp Current (Nom)	18 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	2 kWh
Product Data	
Full product code	871869671392100
Order product name	CorePro LEDcapsule ND 1.9-25W G9 827

CorePro LEDcapsule MV

EAN/UPC - Product	8718696713921
Order code	929001323802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12

Material Nr. (12NC)	929001323802
Net Weight (Piece)	0.012 kg


Dimensional drawing




G9 230V 2.5W-25W 204lm 2700K G9 Non-Dim

Product	D	C
CorePro LEDcapsule ND 1.9-25W G9 827	16.5 mm	48 mm

Photometric data




General Uniform Lighting
1-LED 2.5W-25W G9 827
Page 17



CorePro LEDcapsule MV 25W G9 827 Capsule


CorePro LEDcapsule MV 25W G9 827 Capsule




CorePro LEDcapsule MV 25W G9 827 Capsule

CorePro LEDcapsule MV

Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

