



# Classic filament LED candles and lusters

## Classic LEDCandle ND 2-25W BA35 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	E14 [ E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	2-25W
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	125.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	2 W

Lamp Current (Nom)	20 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	36 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Saving Product	Yes
Suitable For Accent Lighting	No

# Classic filament LED candles and lusters

Energy Consumption kWh/1000 h	2 kWh
<b>Product Data</b>	
Full product code	871869657409600
Order product name	Classic LEDCandle ND 2-25W BA35 E14 827 CL
EAN/UPC - Product	8718696574096
Order code	929001238402

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001238402
Net Weight (Piece)	0.014 kg



## Dimensional drawing



Product	D	C
Classic LEDCandle ND 2-25W BA35 E14 827 CL	35 mm	123 mm


### filament 2.5W-25W 250lm NAD 2700K E14ND

## Photometric data



### LED Lamps, Lightcolour /827 ND CL

### Classic LEDCandle ND 2-25W BA35 827 CL



### Classic LEDCandle ND 2-25W BA35 827 CL

## Classic filament LED candles and lusters

