



Decorative LEDbulbs

CLA LEDBulb D 7.5-48W A60 B22 820 GOLD

The new Deco collection (bulb) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

Product data

General Information	
Cap-Base	B22 [B22]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	7.5-48W
Light Technical	
Color Code	820 [CCT of 2000K]
Luminous Flux (Nom)	610 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	81.33 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	7.5 W
Lamp Current (Nom)	36 mA
Wattage Equivalent	48 W


Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Amber
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871869670958000
Order product name	CLA LEDBulb D 7.5-48W A60 B22 820 GOLD
EAN/UPC - Product	8718696709580

Decorative LEDbulbs

Order code	929001333002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001333002

Net Weight (Piece)	0.030 kg
--------------------	----------


Dimensional drawing




Bulb A60 230V 7.5-48W600lm 2000K D Amber

Product	D	C
CLA LEDBulb D 7.5-48W A60 B22 820 GOLD	60 mm	102 mm


Photometric data



LEDbulb 48W B22 820 GOLD A60



LEDbulb 48W E27 820 GOLD A60




LEDbulb 40W E27 827 CL A60 D

Decorative LEDbulbs

Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

