

# MASTER TL5 High Output

## MASTER TL5 HO 80W/865 SLV/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

### Product data

General Information	
Cap-Base	G5 [ G5]
Life to 50% Failures Preheat (Nom)	30000 h
Features	na [ Not Applicable]
System Description	High Output
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Color Code	865 [ CCT of 6500K]
Luminous Flux (Nom)	6300 lm
Luminous Flux (Rated) (Nom)	6300 lm
Color Designation	Cool Daylight
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	83 lm/W
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	79 lm/W

Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

### Operating and Electrical

Power (Nom)	80 W
Lamp Current (Nom)	0.530 A

### Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

# MASTER TL5 High Output

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Cap-Base Information	Green Plate
----------------------	-------------

## Approval and Application


Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	88 kWh

## Product Data

Full product code	871150071047555
-------------------	-----------------

Order product name	MASTER TL5 HO 80W/865 SLV/40
EAN/UPC - Product	8711500710475
Order code	927929586557
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927929586557
Net Weight (Piece)	127.400 g
ILCOS Code	FDH-80/65/1B-L/P-G5-16/1450

## Dimensional drawing




## Product


MASTER TL5 HO 80W/865 SLV/40

## TL5 HO 80W/865

## Photometric data





LDPB\_TL5-HO8\_865-Spectral power distribution B/W



LDPO\_TL5-HO8\_865-Spectral power distribution Colour


# MASTER TL5 High Output

## Lifetime



LDLE\_TL5-HO8\_0001-Life expectancy diagram

LDLE\_TL5-HO8\_0002-Life expectancy diagram



LDLM\_TL5-HO8\_0001-Lumen maintenance diagram

