



MASTER VALUE LEDspot MV

MASTER LED spot VLE D 4.9-50W GU10 927 36D

Delivering a warm, halogen-like accent beam, MASTER VALUE LEDspot MV is a perfect for spot lighting. Thanks to its high CRI, it realizes more natural colors, enabling cozy and comfortable ambience for residential, hospitality and emphasize the beauty of merchandise in retail. These LEDspots have the familiar look and feel of glass spots, keeping the classic beauty of glass spots and adding the strong performance from LED technology. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers.

Product data

General Information		Luminous Flux in 90° Cone (Rated)	
Cap-Base	GU10 [GU10]		355 lm
EU RoHS compliant	Yes	Operating and Electrical	
Nominal Lifetime (Nom)	25000 h	Input Frequency	50 to 60 Hz
Switching Cycle	50000X	Power (Nom)	4.9 W
Technical Type	4.9-50W	Lamp Current (Nom)	27 mA
Light Technical		Wattage Equivalent	50 W
Color Code	927	Starting Time (Nom)	0.5 s
Beam Angle (Nom)	36 °	Warm Up Time to 60% Light (Nom)	0.5 s
Luminous Flux (Nom)	355 lm	Power Factor (Nom)	0.8
Luminous Intensity (Nom)	650 cd	Voltage (Nom)	220-240 V
Color Designation	Warm White (WW)	Temperature	
Correlated Color Temperature (Nom)	2700 K	T-Case Maximum (Nom)	80 °C
Luminous Efficacy (rated) (Nom)	80.61 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	Yes
Color Rendering Index (Nom)	90		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

MASTER VALUE LEDspot MV

Approval and Application

Energy Efficiency Label (EEL)	A+
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh

Product Data

Full product code	871869670785200
Order product name	MASTER LED spot VLE D 4.9-50W GU10 927 36D

EAN/UPC - Product	8718696707852
Order code	929001348802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001348802
Net Weight (Piece)	0.038 kg


Dimensional drawing




GU10 230V5W-50W 345lm 36D 2700K GU10 Dim

Product	D	C
MASTER LED spot VLE D 4.9-50W GU10 927 36D	50 mm	54 mm

Photometric data



MASTER LEDspotMV 50W GU10 927 36D 355lm





MASTER LEDspotMV 35W GU10 927 36D 260lm

MASTER VALUE LEDspot MV

Photometric data

MASTER LEDspotMV 50W GU10 36D 355lm

Lifetime



MASTER LEDspotMV GU10 922-927 36D

MASTER LEDspotMV GU10 922-927 36D

