



# Classic filament LED candles and lusters

## Classic LEDCandle D 5-40W B35 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	E14 [ E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	5-40W
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	94.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	5 W

Lamp Current (Nom)	38 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	5 kWh


# Classic filament LED candles and lusters

## Product Data

Full product code	871869670982500
Order product name	Classic LEDCandle D 5-40W B35 E14 827 CL
EAN/UPC - Product	8718696709825
Order code	929001332102
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001332102
Net Weight (Piece)	0.014 kg


## Dimensional drawing




CandleB35 230V4.5-40W470lm 2700K D Clear

Product	D	C
Classic LEDCandle D 5-40W B35 E14 827 CL	35 mm	103 mm


## Photometric data



LEDbulb, Bulb A21 14W, 18W 2200-2700K




LEDbulb 40W E14 827 CL B35




LEDbulb 40W E14 827 CL B35

# Classic filament LED candles and lusters

## Lifetime



LEDbulb 40W E27 827 CL A60 D



LEDbulb 40W E27 827 CL A60 D

