

2038X

Colorful textured design

Fast connectivity

Big display

Quality camera



DESIGN

Dimensions: 124mm x 51.5mm x 12.75mm

Weight: 88 gr

Finish: Charmillie 24

Colors available:

- Pure White
- Cocoa Grey

DISPLAY

2.4" QVGA 320 x 240 pixels

TFT 262K display

BATTERY

Battery 950mAh

Talk time - 8h (2G)/ 4h (3G)

Standby time – 160h

Charging time – 2.5h

CAMERA

VGA camera

Video capture: QCIF @15fps

Video playback : QVGA @25fps

PIM

Phone Directory – 1000 entries

SMS capacity - 500

C star input (text prediction mode)

MMS, Calendar, Call Filter, Fake Call, Notes,

Convertor, Alarm, Calculator, Recorder, Voice Alarm,

FM recording, Black/White list, My files, Torchlight

FEATURES

GSM: 850/900/1800/1900

3G network: UMTS 850/900/1800/1900

GPRS: 12

Chipset SC7701B

CPU frequency: 460MHz

OS: ThreadX

Bluetooth: 2.1 + EDR

Internal Memory: 128MB ROM + 64MB RAM

End user memory: 25MB

Micro SD support up to 32GB

FM Radio, 3.5 mm audio jack

WAP, Gameloft Games

Mini SIM & Micro SIM

IN PACK

950mAh Battery

5V 550mA charger (MoU)

Micro USB cable

Headset

Quick Guide

2038X



Pure
White

Cocoa
Grey