



Product Data Sheet

Waterproof Digital HACCP Thermometer with Probe

Functions:

- Supplied with 2 point Calibration Certificate (at 0°C and 100°C)
- High/Low temperature alarm
- Calibration function
- Backlight
- Max/Min recording
- Magnet fitted to back
- Auto power off
- Handheld, flip stand and hanging hook
- Supplied with protective pouch

Product Specifications:

- Measuring Range:** -40°C to 300°C/-40°F to 572°F
- Accuracy:** ±0.5°C (-10°C to 100°C)
± 1°C (-20°C to -10°C & 100°C to 150°C)
otherwise ± 2°C
- Resolution:** 0.1°C(0.1°F)
- Cable:** 1.35m
- Probe Size:** 4mmØ x 150mm
- Cable Parameters:** Max Temp: 200°C (handle: 100°C)
Do not use near open flame
- Battery:** CR2032 x 2pcs Lithium button battery
- Battery Life:** Approx 1500 hours
- Response time:** 6 seconds
- Waterproof:** IP68
- CE/ROHS/WEEE:** Compliant
- Hazard Information (SDS):** See www.brannan.co.uk for information
- Component Weights:** Meter Net Weight: 140.5g (incl. batteries)
Card/Paper Weight: 52.0g (incl. box, instructions & calibration certificate)
Pouch Weight: 37.5g
Gross Weight: 230g
- Product Dimensions:** 106mm x 54mm x 23.5mm (main unit)
- Gross(Box) Dimensions:** 310 x 140 x 30mm



Description	Barcode	Product No
Waterproof Digital HACCP Thermometer	5 011405 386007	38/600/0