

TECHNICAL INFORMATION

Input Power:	AC:100-265V, 50/60Hz
Long Life:	20,000 Hours
LED Chip Type:	SMD
Operation Temperature:	-25°C to +50°C
Dimmable:	No
Beam Angle:	120°
Color:	6000K
Dimension:	8mm
Watts per meter:	10
Lumens per meter:	1000
Current per meter:	1.5A
No. Of Led:	60
Roll Qty:	5M


STRIPLIGHT KITS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 2546 -

[View more details](#)



FEATURES

- 6000K LED Strip light Kit with power adapter
- Includes 5 meter roll striplight with power adapter with plug and play connection
- Flexible installation: Cutting and reconnect the strip as you wish to suit your application
- High-quality resistors for extremely lower voltage drops and efficient current control
- Standard Copper strip for excellent conductivity and heat dissipation
- IP20 rated striplight, perfect for indoor applications
- Hassle free Plug and Play operation
- Suitable for illuminating borders, edges, cabinets, bars and areas with limited space for installation
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

PACKAGING

Gross Weight (Kgs): 0.602
Unit CBM: 0.00315
Dimension: 8mm

MASTER BOX PACKAGING

Box Qty: 20
Length (Box) mm: 190
Width (Box) mm: 65
Height (Box) mm: 210

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157626811

CE/EMC

