



TECHNICAL INFORMATION

| | |
|------------------------|----------------------|
| Plug Type: | BS Plug |
| Watts: | 10 |
| Color: | RGB+W |
| Lumens: | 1000 |
| Beam Angle: | 120° |
| Input Power: | AC:100-240V, 50/60Hz |
| Long Life: | 20,000 Hours |
| Dimension: | 8mm |
| CRI: | >80 |
| Operation Temperature: | -20°C to +45°C |
| No. Of Led: | 60 |
| LED Chip Type: | SMD |


STRIP KIT SMART LIGHT

WiFi-supported home solutions to convert any device into a smart device, and ultimately convert any home into a smart home. Have a systematic, unified control on all your smart devices through the official V-TAC app, Amazon Alexa, and Google Home.

One brand, endless solutions..testing

SKU: 2586 - 930

[View more details](#)



FEATURES

- Wi-Fi enabled smart striplight
- Easy to install and pair with the V-TAC Smart Light App
- 2.4Ghz Wi-Fi frequency
- Switch lights off, change colours, dim the lights and more using the V-TAC app
- Wireless standard: IEEE 802.11 b/g/n
- Can be controlled via V-TAC Smart Light app or Alexa and Google Home
- BS Plug adapter included
- Suitable for illuminating Borders, Edges, Cabinets, Bars and any area with limited space for installation.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

PACKAGING

Gross Weight (Kgs): 0.13176
Unit CBM: 0.000632
Dimension: 8mm

MASTER BOX PACKAGING

Box Qty: 20
Length (Box) mm: 190
Width (Box) mm: 70
Height (Box) mm: 210

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157643801